

formerly Aquionics, Berson, Hanovia and Orca GmbH

 Patented lamp connector provides user safety and easy servicing








 Sleeves and wiper can be changed quickly and easily by a single operator

# **ProLine PQ AL**


VALIDATED UV TREATMENT FOR DRINKING WATER Our Proline PQ AL UV systems are optimised to deliver effective UV treatment for drinking water. Integraing an innovative multiple low pressure lamp chamber with sensors and intelligent control technology to automatically deliver optimum treatment performance with high operational efficiency. Eliminating harmful microorganisms, reduce the bio-burden, protect against biofouling. Each system comes with a certified dry UV sensor allowing checking of UV performance. The UV sensor measures the germicidal output of the UV system and a UV dose read out makes it easy to monitor and log performance. The control system also has the ability to take flow and transmittance meter inputs and calculate the UV dose based on real time operating conditions.



## POTENTIAL LOCATION OF PROLINE PQ AL™ IN DRINKING WATER TREATMENT PROCESS



KEY FEATURES	WHAT IT GIVES YOU	BENEFITS FOR YOU			
INTELLIGENCE					
UV sensor	Continuous verification of performance with real time red UV dose reading and in-built low UV dose alarm	Easy to monitor and log system performance			
Flow and UV transmittance (UVT) meter inputs	Stepless adjustment of lamp power based on real time operating conditions	Optimised use of energy, saving operating costs			
OPTIMISATION					
Third party validated UV systems tested in accordance with the USEPA UV Disinfection Guidance Manual	UV system dose equations and sizing have been independently derived	Confidence the system will perform as stated			
Multiple low pressure lamps	Provides optimum wavelength to treat your drinking	Does not affect taste and odour			
	water	No chemicals			
	High treatment capacity	Compact footprint and reduced operating cost			
Innovative chamber design	Maximises the water's exposure to UV light	Reduces energy costs			
Designed for treatment of drinking water	Flanged connections, high standard internal finish	Designed to international standards			
	FDA and EC approved seals	Industry compliant materials			
	Automatic wiper	Self cleaning to maintain performance			
INTEGRATION					
Designed for your process	*Skid mountable	Easy to install			
*Option					



MODEL NUMBER	MAX POWE	R (KW)	DIMEN	ISIONS (	MM)								APPROX W	EIGHT (KG)
	Starting	Running		Chamber Control										
			А	В	С	D	E	F	DN	K*	L	M**	Chamber (Empty)	Control Cabinet
ProLine PQ AL 100	2.4	1.2-2.4	1710	1500	420	400	1417	1372	150	300	800	1000	150	70
ProLine PQ AL 300	7.2	3.6-7.2	1800	1500	605	560	1372	1475	250	400	1200	1200	300	140

All dimensions are approximate for clearance purposes only. We have a policy of continuous product development, exact drawings are available on request. All specifications are subject to change without notification. Your distributor or our account manager can advise on correct sizing and specification requirements.

Allow dimension L in front of cabinet for door opening and panel access.

<sup>\*\*</sup> M dimension includes the space for the cabinet mounting brackets but you need to allow space below the cabinet for cable entry and access (minimum of 250 mm).

UV CHAMBER	
Material:	StSt 316L / 1.4404
Internal finish:	As made pipe and tube, <0.8 µm RA, welds ground out, electropolished and passivated
External finish:	Brushed to K280, electropolished and passivated
Process (mating) connections:	Flange EN 1092-1 PN16
Drain connection:	BSP socket
End plate:	Removable end plate
Degree of protection:	IP54 equivalent to NEMA 12 but not for outside use
Arc tube (lamp):	Low pressure
Arc tube enclosure:	Pure quartz (F200)
Number of arc tubes (lamps):	4 (PQ AL 100), 12 (PQ AL 300)
Expected lamp life:	9000 hours
Temperature sensor:	Yes
UV sensor:	Calibrated DVGW compliant dry sensor
Working fluid temperature:	5°C to 40°C
Hydrostatically pressure tested:	Yes
Wiper:	Automatic (electrically driven)
Chamber mounting:	Horizontal only
Operating pressure:	10 bar (positive pressure only)
Seals:	EPDM, ADI free, EC 1935/2004, FDA 21 CFR 177.2600 approved

#### OPTIONS

Document Support Pack

Cabinet material: Stainless steel 304, IP54 (NEMA 12)

Cabinet material: Stainless steel 304 with air conditioning (5-50°C), IP66 (NEMA 4x), relative humidity <95% non condensing. See sales drawings for sizes

Operation and Maintenance manual and printed Installation and Commissioning manual in Chinese, English, French, German and Spanish

Flange options: ANSI 150, JIS, Table 'E'

Lead length: 20 and 29 m

Welder Document Pack for chamber construction

Skid mounting (not ship board or earthquake zone)

Air vent connection

In field UV reference sensor kit

UL 508A labeled for cabinet

CABINET (CONTROLLER UVTC	OUCH)
Material:	Polyester coated carbon steel
Degree of protection:	IP54 / NEMA 12
Supply voltages:	AL 100: 200-277V (-5/+10) 1L+N, 2L 50/60Hz 345-480V (-5/+10) 3L+N, 50/60Hz AL 300: 345-480V (-5/+10) 3L+N, 50/60Hz
Operating temp range:	5°C to 40°C
Relative humidity:	<85% non-condensing
Cooling fans:	Yes
Variable power:	Stepless variable power (50% reduction from maximum ballast power)
Interconnecting cable lengths:	10 m to chamber
CUSTOMER OUTPUTS	
4-20 mA outputs:	UV RED dose, lamp driven output power (%)
VFC outputs:	System ready, system stand by, system running, common warning, common trip, system in remote
CUSTOMER INPUTS	
4-20 mA active or passive inputs:	Flow meter and transmittance meter
VFC inputs:	Remote stop/start, remote reset, remote clear message, remote set power high

Modbus RS 485 serial RTU for SCADA connection

#### **APPROVALS**

CE marked, USEPA (UVDGM)



### **ProLine PQ AL**

Also available in our Drinking Water product range...

PROLINE PQ EO

PROLINE PQ AF

PROLINE PQ IL

PROLINE PQ IL DVGW

Energy Optimised medium pressure range, USEPA validated add, UVT compensation

Small community, low energy amalgam range with USEPA validation Compact medium pressure range with USEPA validation

Compact medium pressure range with DVGW certification

#### Canada

+1 980.256.5700 americas@nuvonicuv.com

#### China

+86 21 61679599 apac@nuvonicuv.com

### Germany

+49 611 44575375 emea@nuvonicuv.com

### Malaysia

+60 16 440 8834 sea@nuvonicuv.com



#### Mexico

+1 980.256.5700 americas@nuvonicuv.com

#### **United Kingdom**

+44 1753 515300 emea@nuvonicuv.com

#### USA

+1 980 256 5700 americas@nuvonicuv.com



A Halma company

formerly Aquionics, Berson, Hanovia and Orca GmbH



